



GRK5 Antibody

CATALOG NUMBER: 48-200

Specifications

SPECIES REACTIVITY:	Bat, Bovine, Chicken, Gibbon, Horse, Human, Monkey, Mouse, Pig, Rat
TESTED APPLICATIONS:	IHC
APPLICATIONS:	GRK5 antibody can be used in Western Blot starting at 1:1000 - 1:4000, immunohistochemistry in frozen tissues starting at 1:200, and immunohistochemistry starting at 1:100.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	BLAST analysis of the peptide immunogen showed no homology with other human proteins.
IMMUNOGEN:	GRK5 antibody was raised against a peptide located near the internal domain of GRK5 (Human).
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
PHYSICAL STATE:	Liquid
BUFFER:	PBS, 0.1% sodium azide.
STORAGE CONDITIONS:	GRK5 antibody should be stored long term (months) at -80 °C and short term (days) at 4 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	GRK5, FP2025, GPRK5
ACCESSION NO.:	P34947
PROTEIN GI NO.:	462203
OFFICIAL SYMBOL:	GRK5
GENE ID:	2869

Background

FOR RESEARCH USE ONLY

December 13, 2016