

Name: Rabbit polyclonal DYN1 (Ser778) antibody(Phospho-specific)
Product Data Sheet - PHOSPHO**Catalog: TA313758**

Components:	• Rabbit polyclonal DYN1 (Ser778) antibody(Phospho-specific) (TA313758)
Amount:	100ul
Immunogen:	The antiserum was produced against synthesized phosphopeptide derived from human DYN1 around the phosphorylation site of serine 778 (T-S-SP-P-T).
Host:	Rabbit
Isotype:	IgG
Species Reactivity:	Human, Mouse, Rat
Guaranteed Applications:	WB
Suggested Dilutions:	WB: 1:500~1:3000, ELISA: 1:20000
Concentration:	1mg/ml
Buffer:	Phosphate buffered saline (without Mg ²⁺ and Ca ²⁺), pH 7.4, 150mM NaCl, 0.02% sodium azide and 50% glycerol.
Purification:	The antibody was affinity-purified from rabbit antiserum by affinity-chromatography using epitope-specific immunogen.
Storage Condition:	Shipped at -20C. Upon delivery store at -20C. Dilute in PBS (pH7.3) if necessary. Stable for 12 months from date of receipt. Avoid repeated freeze-thaws.


Target

Target Name:	Homo sapiens dynamin 1 (DNM1), transcript variant 1
Alternative Name:	DNM
Database Link:	NP_004399
Function:	


This product is to be used for laboratory only. Not for diagnostic or therapeutic use.

© 2014 OriGene Technologies, Inc. 9620 Medical Center Dr., Suite 200, Rockville, MD 20850

Validation Data



Western blot analysis of extracts from Mouse brain cells, using DYN1 (Phospho-Ser778) antibody. The lane on the right is treated with the synthesized peptide.



Western blot analysis of extracts from HepG2 cells (Lane 2), using DYN1 (Phospho-Ser778) Antibody. The lane on the left is treated with synthesized peptide.

* More validation images may be available on our website: <http://www.origene.com/antibody/TA313758.aspx>